



Classic frosted LED candles and lusters



CLA LEDCandle ND 2.2-25W BA35 E14 FR

Featuring a classic heritage design, Classic forsted LED candles and lusters deliver beautiful, decorative warm-white light while saving around 90% on energy costs. The familiar shapes of Classic forsted LED candles and lusters are a perfect fit for your existing fixtures.

Product data

General Information	
Cap-Base	E14 [E14]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
Flux measurement reference	Sphere
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	250 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	113.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz


Input Frequency	50 to 60 Hz
Power Consumption	2.2 W
Lamp Current (Nom)	21 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	36 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	BA35

Classic frosted LED candles and lusters

Approval and Application	
Energy Efficiency Class	E
Energy Consumption kWh/1000 h	3 kWh
EPREL Registration Number	387387
EyeComfort	Yes

Product Data	
Order product name	CLA LEDCandle ND 2.2-25W BA35 E14 FR
Full product name	CLA LEDCandle ND 2.2-25W BA35 E14 FR

Dimensional drawing




Photometric data


Spectral Power Distribution Colour - CLA LEDCandle ND 2.2-25W BA35 E14 FR

Full product code	871869670649700
Order code	929001345802
Material Nr. (12NC)	929001345802
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696706497
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696706503

Product	D	C
CLA LEDCandle ND 2.2-25W BA35 E14 FR	35 mm	123 mm




General uniform lighting - CLA LEDCandle ND 2.2-25W BA35 E14 FR




Light Distribution Diagram - CLA LEDCandle ND 2.2-25W BA35 E14 FR

Classic frosted LED candles and lusters

Lifetime



Life Expectancy Diagram - CLA LEDCandle ND 2.2-25W BA35 E14 FR



Lumen Maintenance Diagram - CLA LEDCandle ND 2.2-25W BA35 E14 FR

