



MASTER LEDspot ExpertColor MV



MASTER LED ExpertColor 3.9–35W GU10 940 36D

MASTER LEDspot MV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates ambience with superior lighting that has a customised spectrum, high CRI and deep dimming features. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will also suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot LV lamps.

Product data

General Information	
Cap base	GU10
Nominal lifetime	40,000 h
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Narrow Cone
CE mark	Yes
EU RoHS compliant	Yes

Light Technical	
Colour Code	940 [CCT of 4000K]
Beam angle (nom.)	36 degree(s)
Luminous Flux	300 lm
Luminous intensity (nom.)	600 cd
Colour designation	Cool White (CW)
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	76.00 lm/W
Colour consistency	<3

Colour rendering index (CRI)	97
LLMF at end of nominal lifetime (nom.)	70 %
Luminous flux in 90° cone (rated)	300 lm
Flickering value (PstLM)	1
Stroboscopic effect	0.4
Photobiological safety according to EN 62471	RG1


Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	3.9 W
Lamp current (nom.)	22 mA
Wattage equivalent	35 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (nom.)	220–240 V

MASTER LEDspot ExpertColor MV

Temperature	
T-Case maximum (nom.)	80 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	PAR16
Approval and Application	
Energy Efficiency Class	F
Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	4 kWh
EPREL registration number	391831
EyeComfort	Yes



Application Conditions	
Can it be used in closed luminaires	No
Product Data	
Order product name	MAS LED ExpertColor 3.9-35W GU10 940 36D
Full product name	MASTER LED ExpertColor 3.9-35W GU10 940 36D
Full EOC	871869670759300
Order code	70759300
Material no. (12 NC)	929001346902
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696707593
Numerator – packs per outer box	10
EAN/UPC – Case	8718696707609

Dimensional drawing



Product	D	C
MAS LED ExpertColor 3.9-35W GU10 940 36D	50 mm	54 mm

Photometric data




Accent Lighting Spots - MAS LED ExpertColor 3.9-35W GU10 940 36D

Spectral Power Distribution Colour - MAS LED ExpertColor 3.9-35W GU10 940 36D


MASTER LEDspot ExpertColor MV

Photometric data




Light Distribution Diagram - MAS LED ExpertColor 3.9-35W GU10 940 36D

Lifetime



Life Expectancy Diagram - MAS LED ExpertColor 3.9-35W GU10 940 36D



Lumen Maintenance Diagram - MAS LED ExpertColor 3.9-35W GU10 940 36D

