



# MASTER LEDspot ExpertColor MV

## MAS LED ExpertColor 5.5-50W GU10 927 25D

MASTER LEDspot ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. They offer superior lighting that has a customized spectrum, high CRI, and deep dimming feature. What's more the innovative, trimless lens design will also suit almost any interior decor with its clean and neat look. In addition, with MASTER LEDspot ExpertColor you can take advantage of the full ExpertColor family, which also includes LEDspot MR16, LEDspot AR111 and LEDspot PAR lamps. MASTER LEDspot ExpertColor delivers huge energy savings and minimizes maintenance costs without any compromise on light quality and lifetime, enabling residential and business owners to achieve a return on their investment within a short time period.

### Product data

General Information	
Cap-Base	GU10
Nominal lifetime	40,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Narrow Cone
CE mark	Yes
EU RoHS compliant	Yes
Light Technical	
Color Code	927
Beam Angle (Nom)	25 degree(s)
Luminous Flux	355 lm
Luminous Intensity (Nom)	1,000 cd
Color Designation	Warm White (WW)

Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	64.55 lm/W
Color Consistency	<3
Color rendering index (CRI)	97
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	355 lm
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Photobiological safety according to EN 62471	RG1

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	5.5 W

# MASTER LEDspot ExpertColor MV

Lamp Current (Nom)	30 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V

## Temperature

T-Case Maximum (Nom)	80 °C
----------------------	-------

## Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

## Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	PAR16

## Approval and Application

Energy Efficiency Class	G
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	6 kWh

EPREL Registration Number	544212
EyeComfort	Yes


## Application Conditions

can it be used in closed luminaires	No
-------------------------------------	----

## Product Data


Order product name	MAS LED ExpertColor 5.5-50W GU10 927 25D
Full product name	MAS LED ExpertColor 5.5-50W GU10 927 25D
Full product code	871869670761600
Order code	929001347002
Material Nr. (12NC)	929001347002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696707616
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696707623

## Dimensional drawing




Product	D	C
MAS LED ExpertColor 5.5-50W GU10 927 25D	50 mm	54 mm

## Photometric data



CONEXPO-AG 11 Photo Lighting ETC Page 111




Accent Lighting Spots - MAS LED ExpertColor 5.5-50W GU10 927 25D

Spectral Power Distribution Colour - MAS LED ExpertColor 5.5-50W GU10 927 25D

# MASTER LEDspot ExpertColor MV

## Photometric data



Light Distribution Diagram - MAS LED ExpertColor 5.5-50W GU10 927 25D

## Lifetime



Life Expectancy Diagram - MAS LED ExpertColor 5.5-50W GU10 927 25D



Lumen Maintenance Diagram - MAS LED ExpertColor 5.5-50W GU10 927 25D

