



# MASTER VALUE LEDspot MV

# Master LED 4.9-50W GU10 940 36D Dim

Delivering a warm, halogen-like accent beam, MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it realizes more natural colors, creating cozy and comfortable ambiences for residential and hospitality projects, and emphasizing the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. MASTER VALUE also offers more energy savings that normal LED spots.

### **Warnings and Safety**

- · Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

### **Product data**

General Information	
Cap-Base	GU10
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	940 [CCT of 4000K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	420 lm

Luminous Intensity (Nom)	700 cd
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	84.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	380 lm
Operating and Electrical	
Line Frequency	50 to 60 Hz


Datasheet, 2023, April 16 data subject to change

# **MASTER VALUE LEDspot MV**

Input Frequency	50 to 60 Hz	
Power Consumption	5 W	
Lamp Current (Nom)	27 mA	
Wattage Equivalent	50 W	
Starting Time (Nom)	0.5 s	
Warm-up time to 60% light	0.5 s	
Power Factor (Fraction)	0.8	
Voltage (Nom)	220-240 V	
Temperature		
T-Case Maximum (Nom)	80 ℃	
Controls and Dimming		
Dimmable	Yes	
Mechanical and Housing		
Bulb Shape	PAR16	


Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	5 kWh
Product Data	
Order product name	Master LED 4.9-50W GU10 940 36D Dim
Full product name	Master LED 4.9-50W GU10 940 36D Dim
Full product code	871869675594500
Order code	929001349008
Material Nr. (12NC)	929001349008
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696755945
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696755952

# Dimensional drawing




Product	D	С
Master LED 4.9-50W GU10 940 36D Dim	50 mm	54 mm

### Photometric data




Accent Lighting Spots - Master LED 4.9-50W GU10 940 36D Dim



Spectral Power Distribution Colour - Master LED 4.9-50W GU10 940 36D Dim


# **MASTER VALUE LEDspot MV**


### Photometric data



Light Distribution Diagram - Master LED 4.9-50W GU10 940 36D Dim

## Lifetime





Life Expectancy Diagram - Master LED 4.9-50W GU10 940 36D Dim

Lumen Maintenance Diagram - Master LED 4.9-50W GU10 940 36D Dim



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.