





## MAS LED spot VLE D 4.9-50W GU10 927 60D

Delivering a warm, halogen-like accent beam, MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it realizes more natural colors, creating cozy and comfortable ambiences for residential and hospitality projects, and emphasizing the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. MASTER VALUE also offers more energy savings that normal LED spots.

#### Warnings and Safety

- · Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

#### **Product data**

General Information	
Cap-Base	GU10
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Narrow Cone
CE mark	Yes
EU RoHS compliant	Yes
Light Technical	
Color Code	927


Beam Angle (Nom)	60 degree(s)
Luminous Flux	355 lm
Luminous Intensity (Nom)	400 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	80.61 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	355 lm

Datasheet, 2024, March 14 data subject to change

Flickering value (PstLM) - Flickering value as	1
per EN 61000-3-3	
Stroboscopic effect visibility measure (SVM)	0.4
Photobiological safety according to EN 62471	RG1
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	4.9 W
Lamp Current (Nom)	27 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Shape	PAR16


Approval and Application	
Energy Efficiency Class	F
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	5 kWh
EPREL Registration Number	391890
EyeComfort	Yes
<b>Application Conditions</b>	
can it be used in closed luminaires	No
Product Data	
Order product name	MAS LED spot VLE D 4.9-50W GU10
	927 60D
Full product name	MAS LED spot VLE D 4.9-50W GU10
	927 60D
Full product code	871869670791300
Order code	929001349102
Material Nr. (12NC)	929001349102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696707913
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696707920

## Dimensional drawing




Product	D	С
MAS LED spot VLE D 4.9-50W GU10 927 60D	50 mm	54 mm

### Photometric data




Calculate Proteometrics 43 Philips Lighting B.V. Page:

Accent Lighting Spots - MAS LED spot VLE D 4.9-50W GU10 927 60D





Spectral Power Distribution Colour - MAS LED spot VLE D 4.9-50W GU10 927 60D



Light Distribution Diagram - MAS LED spot VLE D 4.9-50W GU10 927 60D

#### Lifetime





Life Expectancy Diagram - MAS LED spot VLE D 4.9-50W GU10 927 60D

Lumen Maintenance Diagram - MAS LED spot VLE D 4.9-50W GU10 927 60D

3



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.