



MASTER VALUE LEDspot MV

MAS LED spot VLE DT 3.7–35W GU10 927 36D

Delivering a warm, halogen-like accent beam, MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it realizes more natural colors, creating cozy and comfortable ambiances for residential and hospitality projects, and emphasizing the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. MASTER VALUE also offers more energy savings than normal LED spots.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information			
Cap-Base	GU10 [GU10]	Luminous Intensity (Nom)	500 cd
Nominal lifetime	25,000 hour(s)	Color Designation	Warm White (WW)
Switching Cycle	50,000	Correlated Color Temperature (Nom)	2700 K
Lighting Technology	LED	Luminous Efficacy (rated) (Nom)	78.38 lm/W
EU RoHS compliant	Yes	Color Consistency	<6
		Color rendering index (CRI)	90
		LLMF At End Of Nominal Lifetime (Nom)	70 %
		Luminous Flux in 90° Cone (Rated)	260 lm
Light Technical		Operating and Electrical	
Color Code	922-927 [CCT of 2200K-2700K]	Line Frequency	50 to 60 Hz
Beam Angle (Nom)	36 degree(s)		
Luminous Flux	260 lm		

MASTER VALUE LEDspot MV

Input Frequency	50 to 60 Hz
Power Consumption	3.7 W
Lamp Current (Nom)	20 mA
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V

Temperature

T-Case Maximum (Nom)	80 °C
----------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Shape	PAR16 [PAR 2 inch/50mm]
------------	-------------------------


Approval and Application

Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	4 kWh
EyeComfort	Yes

Product Data


Order product name	MAS LED spot VLE DT 3.7-35W GU10 927 36D
Full product name	MAS LED spot VLE DT 3.7-35W GU10 927 36D
Full product code	871869670809500
Order code	929001350002
Material Nr. (12NC)	929001350002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696708095
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696708101

Dimensional drawing




Product	D	C
MAS LED spot VLE DT 3.7-35W GU10 927 36D	50 mm	54 mm

Photometric data




Spectral Power Distribution Colour - MAS LED spot VLE DT 3.7-35W GU10 927 36D



Light Distribution Diagram - MAS LED spot VLE DT 3.7-35W GU10 927 36D

MASTER VALUE LEDspot MV


Photometric data




Technical Parameters 43 Philips Lighting B.V. Page 107

Accent Lighting Spots - MAS LED spot VLE DT 3.7-35W GU10 927 36D

Lifetime



Life Expectancy Diagram - MAS LED spot VLE DT 3.7-35W GU10 927 36D



Lumen Maintenance Diagram - MAS LED spot VLE DT 3.7-35W GU10 927 36D

