



# Standard LED spots GU10

## LEDspot 50W GU10 2700K 100-240V 36D ND

Standard and Glass LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 socket and are designed as a retrofit replacement for halogen spots. Standard and Glass LEDspots are the perfect solution for your basic lighting needs: they provide the beautiful light and performance you expect from the LED technology at an affordable price.

### Product data


General Information		Operating and Electrical	
Cap-Base	GU10 [GU10]	Line Frequency	50 to 60 Hz
Nominal lifetime	25,000 hour(s)	Input Frequency	50 to 60 Hz
Switching Cycle	15,000	Power Consumption	6 W
Lighting Technology	LED	Wattage Equivalent	50 W
EU RoHS compliant	Yes	Starting Time (Nom)	0.5 s
Light Technical		Warm-up time to 60% light	0.5 s
Color Code	827 [CCT of 2700K]	Power Factor (Fraction)	0.7
Beam Angle (Nom)	36 degree(s)	Voltage (Nom)	100-240 V
Luminous Flux	525 lm	Temperature	
Luminous Intensity (Nom)	1,000 cd	T-Case Maximum (Nom)	70 °C
Color Designation	Warm White (WW)	Controls and Dimming	
Correlated Color Temperature (Nom)	2700 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	87.50 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Shape	PAR16 [PAR 2 inch/50mm]
Color rendering index (CRI)	80		
LLMF At End Of Nominal Lifetime (Nom)	70 %		

Standard LED spots GU10

Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	LEDspot 50W GU10 2700K 100-240V 36D ND
Full product name	LEDspot 50W GU10 2700K 100-240V 36D ND
Full product code	871869672622800



Order code	929001368711
Material Nr. (12NC)	929001368711
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696726228
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696726235

Dimensional drawing



Product	D	C
LEDspot 50W GU10 2700K 100-240V 36D ND	50 mm	54 mm

Photometric data



Spectral Power Distribution Colour - LEDspot 50W GU10 2700K 100-240V 36D ND

Accent Lighting Spots - LEDspot 50W GU10 2700K 100-240V 36D ND

