

Classic filament LEDbulbs

CLA LEDBulb ND 8-75W B22 WW A60 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data


General Information	
Cap-Base	B22 [B22]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	1,055 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	131.88 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz

Power Consumption	8 W
Lamp Current (Nom)	60 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	48 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A60 [A 60mm]
Approval and Application	
Energy Consumption kWh/1000 h	8 kWh

Classic filament LEDbulbs

Product Data	
Order product name	CLA LEDBulb ND 8-75W B22 WW A60 CL
Full product name	CLA LEDBulb ND 8-75W B22 WW A60 CL
Full product code	871869674263100
Order code	929001384202
Material Nr. (12NC)	929001384202


Dimensional drawing




Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696742631
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696742648

Product	D	C
CLA LEDBulb ND 8-75W B22 WW A60 CL	60 mm	104 mm


Photometric data



Spectral Power Distribution Colour - CLA LEDBulb ND 8-75W B22 WW A60 CL




General uniform lighting - CLA LEDBulb ND 8-75W B22 WW A60 CL




Light Distribution Diagram - CLA LEDBulb ND 8-75W B22 WW A60 CL

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - CLA LEDBulb ND 8-75W B22 WW A60 CL



Lumen Maintenance Diagram - CLA LEDBulb ND 8-75W B22 WW A60 CL

