



Classic filament LEDbulbs

CLA LEDBulb ND 7-60W E27 WW G93 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information			
Cap-Base	E27 [E27]	Input Frequency	50 to 60 Hz
Nominal lifetime	15,000 hour(s)	Power Consumption	7 W
Switching Cycle	20,000	Lamp Current (Nom)	60 mA
Lighting Technology	LED	Wattage Equivalent	60 W
Flux measurement reference	Sphere	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.5
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)	45 °C
Luminous Flux	806 lm	Controls and Dimming	
Color Designation	Warm White (WW)	Dimmable	No
Correlated Color Temperature (Nom)	2700 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	115.00 lm/W	Bulb Finish	Clear
Color Consistency	<6	Bulb Shape	G93 [G 93mm]
Color rendering index (CRI)	80		
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical			
Line Frequency	50 to 60 Hz		


Classic filament LEDbulbs

Approval and Application	
Energy Efficiency Class	E
Energy Consumption kWh/1000 h	7 kWh
EPREL Registration Number	400289
EyeComfort	Yes

Product Data	
Order product name	CLA LEDBulb ND 7-60W E27 WW G93 CL
Full product name	CLA LEDBulb ND 7-60W E27 WW G93 CL



Full product code	871869674271600
Order code	929001387902
Material Nr. (12NC)	929001387902
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696742716
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696742723

Dimensional drawing



Product	D	C
CLA LEDBulb ND 7-60W E27 WW G93 CL	95 mm	140 mm

Photometric data




General uniform lighting - CLA LEDBulb ND 7-60W E27 WW G93 CL

Spectral Power Distribution Colour - CLA LEDBulb ND 7-60W E27 WW G93 CL


Classic filament LEDbulbs

Photometric data




Light Distribution Diagram - CLA LEDBulb ND 7-60W E27 WW G93 CL

Lifetime



Life Expectancy Diagram - CLA LEDBulb ND 7-60W E27 WW G93 CL



Lumen Maintenance Diagram - CLA LEDBulb ND 7-60W E27 WW G93 CL

