



T8

EasySmart IR Programming Tool 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Product data

General Information	
Lighting Technology	LED
EU RoHS compliant	Yes
Operating and Electrical	
Power Consumption	1 W
Product Data	
Order product name	EasySmart IR Programming Tool 10/1

Full product name	EasySmart IR Programming Tool 10/1
Order code	929001390604
Material Nr. (12NC)	929001390604
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677473501
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677473506