



MASTER VALUE LEDspot MV

MASTER LED spot VLE D 3.7-35W GU10 927 60D

Delivering a warm, halogen-like accent beam, the MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it achieves more natural colours, creating cosy and comfortable ambience for residential and hospitality projects, and emphasising the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. The MASTER VALUE also offers more energy savings than normal LED spots.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information			
Cap base	GU10	Beam angle (nom.)	60 degree(s)
Nominal lifetime	25,000 h	Luminous Flux	270 lm
Switching Cycle	50,000	Luminous intensity (nom.)	300 cd
Lighting Technology	LED	Colour designation	Warm White (WW)
Flux measurement reference	Narrow Cone	Correlated Colour Temperature	2700 K
CE mark	Yes	Luminous efficacy (rated) (nom.)	72.00 lm/W
EU RoHS compliant	Yes	Colour consistency	<6
		Colour rendering index (CRI)	90
		LLMF at end of nominal lifetime (nom.)	70 %
		Luminous flux in 90° cone (rated)	270 lm
		Flickering value (PstLM)	1

MASTER VALUE LEDspot MV

Stroboscopic effect	0.6
Photobiological safety according to EN 62471 RG1	

Operating and Electrical

Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	3.7 W
Lamp current (nom.)	18 mA
Wattage equivalent	35 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (nom.)	220-240 V

Temperature

T-Case maximum (nom.)	70 °C
-----------------------	-------

Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and Housing

Bulb shape	PAR16
------------	-------

Approval and Application

Energy Efficiency Class	F
-------------------------	---

Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	4 kWh
EPREL registration number	1825218
EyeComfort	Yes


Application Conditions

Can it be used in closed luminaires	No
-------------------------------------	----

Product Data

Order product name	MAS LED spot VLE D 3.7-35W GU10 927 60D
Full product name	MASTER LED spot VLE D 3.7-35W GU10 927 60D
Full EOC	871951431226500
Order code	31226500
Material no. (12 NC)	929002979802
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514312265
Numerator – packs per outer box	10
EAN/UPC - Case	8719514312272



Dimensional drawing



Product	D	C
MAS LED spot VLE D 3.7-35W GU10 927 60D	50 mm	54 mm


MASTER VALUE LEDspot MV

Photometric data




Spectral Power Distribution Colour - MAS LED spot VLE D 3.7-35W GU10 927 60D

Accent Lighting Spots - MAS LED spot VLE D 3.7-35W GU10 927 60D




Light Distribution Diagram - MAS LED spot VLE D 3.7-35W GU10 927 60D

Lifetime



Life Expectancy Diagram - MAS LED spot VLE D 3.7-35W GU10 927 60D



Lumen Maintenance Diagram - MAS LED spot VLE D 3.7-35W GU10 927 60D

MASTER VALUE LEDspot MV

