



CorePro LEDspot MV



Corepro LEDspot 550lm GU10 840 120D

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 or E14 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDlamps deliver huge energy savings and minimize maintenance cost.

Product data

| General Information | |
|--|--------------------|
| Cap base | GU10 [GU10] |
| Nominal lifetime | 15,000 h |
| Switching Cycle | 50,000 |
| Lighting Technology | LED |
| Flux measurement reference | Sphere |
| EU RoHS compliant | Yes |
| Light Technical | |
| Colour Code | 840 [CCT of 4000K] |
| Beam angle (nom.) | 120 degree(s) |
| Luminous Flux | 550 lm |
| Colour designation | Cool White (CW) |
| Correlated Colour Temperature | 4000 K |
| Luminous efficacy (rated) (nom.) | 112 lm/W |
| Colour consistency | <6 |
| Colour rendering index (CRI) | 80 |
| LLMF at end of nominal lifetime (nom.) | 70 % |
| Flickering value (PstLM) | 1 |
| Stroboscopic effect | 0.6 |
| Photobiological safety according to EN 62471 | RG1 |

| Operating and Electrical | |
|------------------------------------|--------------------------|
| Line Frequency | 50 to 60 Hz |
| Input frequency | 50 to 60 Hz |
| Power Consumption | 4.9 W |
| Lamp current (nom.) | 40 mA |
| Starting time (nom.) | 0.5 s |
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.5 |
| Voltage (nom.) | 220-240 V |
| Temperature | |
| T-Case maximum (nom.) | 85 °C |
| Controls and Dimming | |
| Dimmable | No |
| Mechanical and Housing | |
| Bulb shape | PAR16 [PAR 2 inch/50 mm] |
| Approval and Application | |
| Energy Efficiency Class | E |
| Suitable for accent lighting | No |
| Energy consumption kWh/1,000 hours | 5 kWh |

CorePro LEDspot MV


| | |
|---------------------------|--------|
| EPREL registration number | 438114 |
| EyeComfort | Yes |

Product Data

| | |
|--------------------|-------------------------------------|
| Order product name | Corepro LEDspot 550lm GU10 840 120D |
| Full product name | Corepro LEDspot 550lm GU10 840 120D |
| Full EOC | 871951430865700 |
| Order code | 30865700 |


| | |
|-----------------------------------|---------------|
| Material no. (12 NC) | 929002981302 |
| SAP numerator – quantity per pack | 1 |
| EAN/UPC – Product/Case | 8719514308657 |
| Numerator – packs per outer box | 10 |
| EAN/UPC - Case | 8719514308664 |

Dimensional drawing




| Product | D | C |
|-------------------------------------|-------|-------|
| Corepro LEDspot 550lm GU10 840 120D | 50 mm | 54 mm |


Photometric data



Spectral Power Distribution Colour - Corepro LEDspot 550lm GU10 840 120D



General uniform lighting - Corepro LEDspot 550lm GU10 840 120D



Light Distribution Diagram - Corepro LEDspot 550lm GU10 840 120D

CorePro LEDspot MV

Lifetime



Life Expectancy Diagram - Corepro LEDspot 550lm GU10 840 120D



Lumen Maintenance Diagram - Corepro LEDspot 550lm GU10 840 120D

