



MASTER LEDspot ExpertColor LV



MASTER LED ExpertColor 7.5–43W MR16 927 24D

MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customised spectrum, high CRI and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV lamps.

Product data


General Information	
Cap base	GU5.3
Nominal lifetime	40,000 h
Switching Cycle	50,000
Lighting Technology	LED
Flux measurement reference	Narrow Cone
CE mark	Yes
EU RoHS compliant	Yes
Light Technical	
Colour Code	927 [CCT of 2700K]
Beam angle (nom.)	24 degree(s)
Luminous Flux	485 lm
Luminous intensity (nom.)	2,400 cd
Colour designation	Warm White (WW)
Correlated Colour Temperature	2700 K
Luminous efficacy (rated) (nom.)	64.00 lm/W
Colour consistency	<3

Colour rendering index (CRI)	92
LLMF at end of nominal lifetime (nom.)	70 %
Luminous flux in 90° cone (rated)	485 lm
Photobiological safety according to EN 62471	RG1
Operating and Electrical	
Line Frequency	- Hz
Input frequency	- Hz
Power Consumption	7.5 W
Lamp current (nom.)	720 mA
Wattage equivalent	43 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (nom.)	ac electronic 12 V


MASTER LEDspot ExpertColor LV

Temperature	
T-Case maximum (nom.)	93 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb shape	MR16
Approval and Application	
Energy Efficiency Class	G
Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	8 kWh
EPREL registration number	624208
EyeComfort	Yes
Application Conditions	
Can it be used in closed luminaires	No

Dimensional drawing




Photometric data



Light Distribution Diagram - MAS LED ExpertColor 7.5-43W MR16 927 24D

Product Data	
Order product name	MAS LED ExpertColor 7.5-43W MR16 927 24D
Full product name	MASTER LED ExpertColor 7.5-43W MR16 927 24D
Full EOC	871951435865200
Order code	35865200
Material no. (12 NC)	929003079702
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514358652
Numerator – packs per outer box	10
EAN/UPC - Case	8719514358669


Product	D	C
MAS LED ExpertColor 7.5-43W MR16 927 24D	50.5 mm	46 mm



Spectral Power Distribution Colour - MAS LED ExpertColor 7.5-43W MR16 927 24D

MASTER LEDspot ExpertColor LV


Photometric data




Technical Information 1.1 Philips Lighting B.V. Page 10

Accent Lighting Spots - MAS LED ExpertColor 7.5-43W MR16 927 24D

Lifetime



Life Expectancy Diagram - MAS LED ExpertColor 7.5-43W MR16 927 24D



Lumen Maintenance Diagram - MAS LED ExpertColor 7.5-43W MR16 927 24D

