



# Twist High Lumen

## TWIST HIGH LUMEN 45W CDL E27 LV 1CT/6

Energy saving lamp in spiral shape, with superior performance (long life, high switching) and high lumen warm bright light. Perfectly suitable to be used in places where high lumen is required, and the lamp is directly visible.

### Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

### Product data


General Information	
Cap-Base	E27 [E27]
Rated Lifetime (Hours)	10,000 hour(s)
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	2,850 lm
Color Designation	Cool Daylight
Chromaticity Coordinate X (Nom)	313
Chromaticity Coordinate Y (Nom)	337
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	63 lm/W
Color rendering index (CRI)	80
Operating and Electrical	
Line Frequency	50 or 60 Hz

Input Frequency	50 or 60 Hz
Power Consumption	45 W
Lamp Current (Nom)	380 mA
Power Factor (Fraction)	0.95
Voltage (Nom)	110-127 V

Product Data	
Order product name	TWIST HIGH LUMEN 45W CDL E27 LV 1CT/6
Full product name	TWIST HIGH LUMEN 45W CDL E27 LV 1CT/6
Full product code	871829167485600
Order code	929676101101
Material Nr. (12NC)	929676101101
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291674856
Numerator - Packs per outer box	6
EAN/UPC - Case	8718291674863

# Twist High Lumen

## Dimensional drawing



Product	D (max)	C (max)	F (max)
TWIST HIGH LUMEN 45W CDL E27 LV 1CT/6	98 mm	207 mm	80.3 mm

