



# Twist High Lumen

## Twister High Lumen 45W CDL E27 LV 1CT/6

Energy saving lamp in spiral shape, with superior performance (long life, high switching) and high lumen warm bright light. Perfectly suitable to be used in places where high lumen is required, and the lamp is directly visible.

### Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

### Product data


| General Information                |                                | Operating and Electrical      |             |
|------------------------------------|--------------------------------|-------------------------------|-------------|
| Cap-Base                           | E27 [E27]                      | Line Frequency                | 50 or 60 Hz |
| Nominal lifetime                   | 10,000 hour(s)                 | Input Frequency               | 50 or 60 Hz |
| Switching Cycle                    | 5,000                          | Power Consumption             | 45 W        |
| Rated Lifetime (Hours)             | 10,000 hour(s)                 | Lamp Current (Nom)            | 350 mA      |
| Lighting Technology                | Compact Fluorescent Integrated | Starting Time (Nom)           | 1.5 s       |
| Light Technical                    |                                | Power Factor (Fraction)       | 0.92        |
| Color Code                         | 865 [CCT of 6500K]             | Voltage (Nom)                 | 110-127 V   |
| Luminous Flux                      | 2,835 lm                       | Controls and Dimming          |             |
| Color Designation                  | Cool Daylight                  | Dimmable                      | No          |
| Chromaticity Coordinate X (Nom)    | 313                            | Approval and Application      |             |
| Chromaticity Coordinate Y (Nom)    | 337                            | Energy Saving Product         | Yes         |
| Correlated Color Temperature (Nom) | 6500 K                         | Mercury (Hg) Content (Max)    | 5 mg        |
| Luminous Efficacy (rated) (Nom)    | 63 lm/W                        | Energy Consumption kWh/1000 h | 45 kWh      |
| Color rendering index (CRI)        | 80                             |                               |             |

# Twist High Lumen

| Product Data        |   |
|---------------------|---|
| Order product name  | Twister High Lumen 45W CDL E27 LV 1CT/6 |
| Full product name   | Twister High Lumen 45W CDL E27 LV 1CT/6 |
| Full product code   | 871869649592600                         |
| Order code          | 929676102801                            |
| Material Nr. (12NC) | 929676102801                            |

|                                 |               |
|---------------------------------|---------------|
| Numerator - Quantity Per Pack   | 1             |
| EAN/UPC - Product/Case          | 8718696495926 |
| Numerator - Packs per outer box | 6             |
| EAN/UPC - Case                  | 8718696495933 |

## Dimensional drawing



| Product                                 | D (max) | C (max) | F (max) |
|---|---------|---------|---------|
| Twister High Lumen 45W CDL E27 LV 1CT/6 | 82 mm   | 200 mm  | 67 mm   |

