



Softone

Softone 11W WW B22 220-240V 1PF/6

Extremely compact covered energy-saving lamp that produces soft white light

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.


Product data

General Information		Operating and Electrical	
Cap base	B22 [B22]	Line Frequency	50 or 60 Hz
Nominal lifetime	10,000 h	Input frequency	50 or 60 Hz
Switching Cycle	30,000	Power Consumption	11.0 W
Rated Lifetime (Hours)	10,000 h	Lamp current (nom.)	80 mA
Lighting Technology	Compact Fluorescent Integrated	Starting time (nom.)	1.0 s
Light Technical		Power Factor (Fraction)	0.6
Colour Code	827 [CCT of 2700K]	Voltage (nom.)	220-240 V
Luminous Flux	580 lm	Controls and Dimming	
Colour designation	Warm White (WW)	Dimmable	No
Chromaticity Coordinate X (Nom)	463	Mechanical and Housing	
Chromaticity Coordinate Y (Nom)	420	Bulb shape	A55 [A 55 mm]
Correlated Colour Temperature	2700 K	Approval and Application	
Luminous efficacy (rated) (nom.)	48 lm/W	Mercury (Hg) content (max.)	2.0 mg
Colour rendering index (CRI)	82	Mercury (Hg) content (nom.)	1.5 mg
LLMF at end of nominal lifetime (nom.)	65 %		

Energy consumption kWh/1,000 hours	11 kWh
Product Data	
Order product name	Softone 11W WW B22 220-240V 1PF/6
Full product name	Softone 11W WW B22 220-240V 1PF/6
Full EOC	871829168192200
Order code	68192200
Material no. (12 NC)	929689128505

Local order code	11BCSOFT10Y
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291681922
Numerator – packs per outer box	6
EAN/UPC – Case	8718291681939

Dimensional drawing



Product	D (max)	C (max)	F (max)
Softone 11W WW B22 220-240V 1PF/6	56.0 mm	107.5 mm	45.5 mm

