



# Softone Globe

## Softone Globe 20W WW E27 G93 1CH/4

Decorative covered energy-saving lamps for consumer applications

### Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

### Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	10,000 hour(s)
Switching Cycle	30,000
Rated Lifetime (Hours)	10,000 hour(s)
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	1,140 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	57 lm/W
Color rendering index (CRI)	82
LLMF At End Of Nominal Lifetime (Nom)	65 %


Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	20.0 W
Lamp Current (Nom)	145 mA
Starting Time (Nom)	1 s
Power Factor (Fraction)	0.6
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	G93 [G 93mm]
Approval and Application	
Mercury (Hg) Content (Max)	2.0 mg
Mercury (Hg) Content (Nom)	1.5 mg

Softone Globe

Energy Consumption kWh/1000 h	20 kWh
Product Data	
Order product name	Softone Globe 20W WW E27 G93 1CH/4
Full product name	Softone Globe 20W WW E27 G93 1CH/4
Full product code	872790085070300
Order code	85070300

Material Nr. (12NC)	929689151701
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900850703
Numerator - Packs per outer box	4
EAN/UPC - Case	8727900850710

Dimensional drawing



Product	C (max)	F (max)
Softone Globe 20W WW E27 G93 1CH/4	153 mm	48.2 mm

