



Downlighter ESaver

Downlighter 8W WW 220-240V GX53 1PF/6

Energy-saving lamps in shapes approximating R50, R60 and R63 incandescent/halogen reflectors

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Product data

General Information	
Cap-Base	GX53 [GX53]
Nominal lifetime	6,000 hour(s)
Switching Cycle	6,000
Rated Lifetime (Hours)	6,000 hour(s)
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	310 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	38 lm/W
Color rendering index (CRI)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %


Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	8.0 W
Lamp Current (Nom)	65 mA
Starting Time (Nom)	0.2 s
Power Factor (Fraction)	0.6
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	GX53
Approval and Application	
Mercury (Hg) Content (Max)	2.0 mg
Mercury (Hg) Content (Nom)	1.5 mg

Downlighter ESaver

Energy Consumption kWh/1000 h	8 kWh
Product Data	
Order product name	Downlighter 8W WW 220-240V GX53 1PF/6
Full product name	Downlighter 8W WW 220-240V GX53 1PF/6
Full product code	872790085087101
Order code	85087101

Material Nr. (12NC)	929689177102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900850871
Numerator - Packs per outer box	6
EAN/UPC - Case	8718291680130

Dimensional drawing



Product	D (max)	C (max)
Downlighter 8W WW 220-240V GX53 1PF/6	75.5 mm	29.5 mm

