



Circular ESaver

Circular ES 24W CDL E27 220-240V 1CT/6

Circular-shaped energy-saving lamp

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Product data


General Information		Operating and Electrical	
Cap-Base	E27 [E27]	Line Frequency	50 or 60 Hz
Nominal lifetime	6,000 hour(s)	Input Frequency	50 or 60 Hz
Switching Cycle	6,000	Power Consumption	24.0 W
Rated Lifetime (Hours)	6,000 hour(s)	Lamp Current (Nom)	190 mA
Lighting Technology	Compact Fluorescent Integrated	Starting Time (Nom)	0.3 s
Light Technical		Warm-up time to 60% light	5-40 s s
Color Code	865 [CCT of 6500K]	Power Factor (Fraction)	0.6
Luminous Flux	1,700 lm	Voltage (Nom)	220-240 V
Color Designation	Cool Daylight	Controls and Dimming	
Chromaticity Coordinate X (Nom)	313	Dimmable	No
Chromaticity Coordinate Y (Nom)	337	Mechanical and Housing	
Correlated Color Temperature (Nom)	6500 K	Bulb Shape	Circular
Luminous Efficacy (rated) (Nom)	68 lm/W	Approval and Application	
Color rendering index (CRI)	80	Mercury (Hg) Content (Max)	5.0 mg
LLMF At End Of Nominal Lifetime (Nom)	70 %		

Circular ESaver

Energy Consumption kWh/1000 h	24 kWh
Product Data	
Order product name	Circular ES 24W CDL E27 220–240V 1CT/6
Full product name	Circular ES 24W CDL E27 220–240V 1CT/6
Full product code	871150031705610
Order code	31705610

Material Nr. (12NC)	929689187201
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500317056
Numerator - Packs per outer box	6
EAN/UPC - Case	8711500317063

Dimensional drawing



Product	D (max)	C (max)	F (max)
Circular ES 24W CDL E27 220–240V 1CT/6	17.5 mm	77.5 mm	227.2 mm

