



Ambiance Globe

AMBIANCE GL 18W WW E27 220-240V 1CT/6

Decorative covered standard energy saving lamp in globe shape. Gives a soft, diffuse light with a high comfort level. Suitable for applications where lamp is visible. Approximates the look of a frosted globe shaped incandescent lamp

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.


Product data

General Information			
Cap-Base	E27 [E27]	Input Frequency	50 or 60 Hz
Rated Lifetime (Hours)	6,000 hour(s)	Power Consumption	18 W
Lighting Technology	Compact Fluorescent Integrated	Lamp Current (Nom)	120 mA
		Power Factor (Fraction)	0.6
		Voltage (Nom)	220-240 V
Light Technical		Mechanical and Housing	
Color Code	827 [CCT of 2700K]	Bulb Shape	GL110 [Globe 110mm]
Luminous Flux	1,000 lm		
Color Designation	Warm White (WW)		
Chromaticity Coordinate X (Nom)	463		
Chromaticity Coordinate Y (Nom)	420		
Correlated Color Temperature (Nom)	2700 K		
Luminous Efficacy (rated) (Nom)	56 lm/W		
Color rendering index (CRI)	82		
Operating and Electrical		Product Data	
Line Frequency	50 or 60 Hz	Order product name	AMBIANCE GL 18W WW E27 220-240V 1CT/6
		Full product name	AMBIANCE GL 18W WW E27 220-240V 1CT/6
		Full product code	871016339039001
		Order code	929689415307
		Material Nr. (12NC)	929689415307
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8710163390390

Ambiance Globe

Numerator - Packs per outer box	6
EAN/UPC - Case	8727900893939

Dimensional drawing



Product	D (max)	C (max)	F (max)
AMBIANCE GL 18W WW E27 220-240V 1CT/6	111 mm	169 mm	50.5 mm

