



# Energy Saver Reflectors

## EL/A R30 15W

Looking for an energy saver that doesn't look like one? The Philips EnergySaver family provides energy efficient lighting options that don't just provide similar light as your standard incandescent light bulb, they also have the same classic shapes. Philips Energy Saver reflector flood compact fluorescents reduce operating costs without sacrificing light quality compared to incandescent equivalents. With dimmable and hard glass options, they are ideal for recessed and track lighting indoors and outdoors.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Rated Lifetime (Hours)	8,000 hour(s)
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	120 degree(s)
Luminous Flux	750 lm
Luminous Intensity (Nom)	200 cd
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	50 lm/W
Color rendering index (CRI)	82

Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	15 W
Lamp Current (Nom)	220 mA
Power Factor (Fraction)	0.55
Voltage (Nom)	110-127 V

Mechanical and Housing	
Bulb Shape	EL/A R30

Approval and Application	
Mercury (Hg) Content (Nom)	3.7 mg

Product Data	
Order product name	EL/A R30 15W
Full product name	EL/A R30 15W
Order code	929689720111

Energy Saver Reflectors

Material Nr. (12NC)	929689720111
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677421397
Numerator - Packs per outer box	6

EAN/UPC - Case	50046677421392
----------------	----------------

Dimensional drawing

Product	D (max)	C (max)	F (max)
EL/A R30 15W	97 mm	142 mm	50.5 mm

