



Energy Saver Outdoor

EL/A PAR38 23W REFLECTOR 2PC

Looking for an energy saver that does not look like one? The Philips EnergySaver Outdoor family provides energy efficient lighting options that don't just provide similar light as your standard incandescent light bulb. Available in reflector flood, bug away, and post varieties. Try the Philips EnergySaver Outdoor family of products and see how they truly provide advanced lighting designed around your needs.


Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Rated Lifetime (Hours)	10,000 hour(s)
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	1,300 lm
Luminous Intensity (Nom)	420 cd
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	56 lm/W
Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	23 W

Lamp Current (Nom)	330 mA
Power Factor (Fraction)	0.55
Voltage (Nom)	110-127 V
Mechanical and Housing	
Bulb Shape	PAR38 2 Pieces
Product Data	
Order product name	EL/A PAR38 23W REFLECTOR 2PC
Full product name	EL/A PAR38 23W REFLECTOR 2PC
Order code	929689721101
Material Nr. (12NC)	929689721101
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677157166
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677157161

Energy Saver Outdoor

Dimensional drawing



Product	D (max)	C (max)	F (max)
EL/A PAR38 23W REFLECTOR 2PC	122 mm	137 mm	43.5 mm

