



# Energy Saver Reflectors

## EL/A PAR38 23W 2PC 4/1

Looking for an energy saver that doesn't look like one? The Philips EnergySaver family provides energy efficient lighting options that don't just provide similar light as your standard incandescent light bulb, they also have the same classic shapes. Philips Energy Saver reflector flood compact fluorescents reduce operating costs without sacrificing light quality compared to incandescent equivalents. With dimmable and hard glass options, they are ideal for recessed and track lighting indoors and outdoors.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Rated Lifetime (Hours)	10,000 hour(s)
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	1,300 lm
Luminous Intensity (Nom)	420 cd
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	56 lm/W
Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz


Power Consumption	23 W
Lamp Current (Nom)	330 mA
Power Factor (Fraction)	0.55
Voltage (Nom)	110-127 V

Mechanical and Housing	
Bulb Shape	PAR38 2 Pieces

Product Data	
Order product name	EL/A PAR38 23W 2PC 4/1
Full product name	EL/A PAR38 23W 2PC 4/1
Order code	929689721102
Material Nr. (12NC)	929689721102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677227913
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677227918

# Energy Saver Reflectors

## Dimensional drawing



Product	D (max)	C (max)	F (max)
EL/A PAR38 23W 2PC 4/1	122 mm	137 mm	43.5 mm

