



# Energy Saver Reflectors

## EL/A R30 EDIM 16W 1CT/6

Looking for an energy saver that doesn't look like one? The Philips EnergySaver family provides energy efficient lighting options that don't just provide similar light as your standard incandescent light bulb, they also have the same classic shapes. Philips Energy Saver reflector flood compact fluorescents reduce operating costs without sacrificing light quality compared to incandescent equivalents. With dimmable and hard glass options, they are ideal for recessed and track lighting indoors and outdoors.

### Product data


General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Switching Cycle	10,000
Rated Lifetime (Hours)	8,000 hour(s)
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Color Code	827 [CCT of 2700K]
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	459
Chromaticity Coordinate Y (Nom)	412
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	38 lm/W
Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	16 W

Lamp Current (Nom)	210 mA
Power Factor (Fraction)	0.65
Voltage (Nom)	110-127 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	EL/A R30
Product Data	
Order product name	EL/A R30 EDIM 16W 1CT/6
Order code	929689768101
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929689768101
Full product name	EL/A R30 EDIM 16W 1CT/6
EAN/UPC - Case	50046677419979

# Energy Saver Reflectors

EAN/UPC - Product/Case	046677419974
------------------------	--------------

## Dimensional drawing



Product	D (max)	C (max)	F (max)
EL/A R30 EDIM 16W 1CT/6	96.0 mm	138.5 mm	48.5 mm

