



Energy Saver Reflectors

EL/A R30 15W 4.1K

Looking for an energy saver that doesn't look like one? The Philips EnergySaver family provides energy efficient lighting options that don't just provide similar light as your standard incandescent light bulb, they also have the same classic shapes. Philips Energy Saver reflector flood compact fluorescents reduce operating costs without sacrificing light quality compared to incandescent equivalents. With dimmable and hard glass options, they are ideal for recessed and track lighting indoors and outdoors.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Rated Lifetime (Hours)	8,000 hour(s)
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	120 degree(s)
Luminous Flux	750 lm
Luminous Intensity (Nom)	200 cd
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	380
Chromaticity Coordinate Y (Nom)	380
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	50 lm/W
Color rendering index (CRI)	82

Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	16 W
Lamp Current (Nom)	220 mA
Power Factor (Fraction)	0.55
Voltage (Nom)	110-127 V


Mechanical and Housing	
Bulb Shape	EL/A R30

Product Data	
Order product name	EL/A R30 15W 4.1K
Full product name	EL/A R30 15W 4.1K
Order code	929689790501
Material Nr. (12NC)	929689790501
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677418625

Energy Saver Reflectors

Numerator - Packs per outer box	6
EAN/UPC - Case	50046677418620

Dimensional drawing



Product	D (max)	C (max)	F (max)
EL/A R30 15W 4.1K	97 mm	142 mm	50.5 mm

