



Energy Saver T2

EL/mdTQ 13W T2 5k

The Philips EnergySaver T2 provides energy efficient lighting in a smaller, sleeker, size that fits more fixtures. The energy saving T2 is a direct replacement for most incandescents, provides soft white light and lasts 11 years* reducing the hassle of frequent replacements.


Product data

| General Information | |
|---------------------------------------|-----------------------------------|
| Cap-Base | E26 [Single Contact Medium Screw] |
| Nominal lifetime | 10,000 hour(s) |
| Switching Cycle | 5,000 |
| Rated Lifetime (Hours) | 10,000 hour(s) |
| Lighting Technology | Compact Fluorescent Integrated |
| Light Technical | |
| Color Code | 850 [CCT of 5000K] |
| Luminous Flux | 860 lm |
| Color Designation | Daylight |
| Chromaticity Coordinate X (Nom) | 346 |
| Chromaticity Coordinate Y (Nom) | 359 |
| Correlated Color Temperature (Nom) | 5000 K |
| Luminous Efficacy (rated) (Nom) | 63 lm/W |
| Color rendering index (CRI) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 50 % |
| Operating and Electrical | |
| Line Frequency | 50 or 60 Hz |
| Input Frequency | 50 or 60 Hz |
| Power Consumption | 13.0 W |
| Lamp Current (Nom) | 210 mA |

| Power Factor (Fraction) | 0.55 |
|---------------------------------|-------------------|
| Voltage (Nom) | 110-127 V |
| Controls and Dimming | |
| Dimmable | No |
| Mechanical and Housing | |
| Bulb Shape | EL/mdTQS |
| Approval and Application | |
| Mercury (Hg) Content (Max) | 2 mg |
| Energy Consumption kWh/1000 h | 13 kWh |
| Product Data | |
| Order product name | EL/mdTQ 13W T2 5k |
| Full product name | EL/mdTQ 13W T2 5k |
| Order code | 414045 |
| Material Nr. (12NC) | 929689799204 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677414047 |
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 50046677414042 |

Energy Saver T2

Dimensional drawing



| Product | D (max) | C (max) | F (max) |
|-------------------|---------|----------|---------|
| EL/mdTQ 13W T2 5k | 51.5 mm | 104.3 mm | 42.5 mm |

