



# ESSENTIAL

## ESSENTIAL 70W CDL E27 220-240V 1CC/6

The Essential range is a standard stick-shape compact fluorescent lamp, with the lowest purchase price. It is available in 8W, 14W, 18W and 23W, with lumen equivalence of 40W, 75W, 100W and 125W incandescent light bulb. It is also available in two color temperatures: warm white (2700K) and cool daylight (6500K). It is available in both 220-240V and 120-127V and able to operate under a wide voltage range (Power supply fluctuation). It consumes up to 80% less energy than the incandescent light bulb and lasts for 3 years.

### 安全提示

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

### 产品数据

| 一般信息          |                                |
|---------------|--------------------------------|
| 底座            | E27 [E27]                      |
| 额定使用寿命 ( 小时 ) | 8,000 小时                       |
| 照明技术          | Compact Fluorescent Integrated |
| 灯技术           |                                |
| 颜色代码          | 865 [CCT of 6500K]             |
| 光通量           | 4,400 lm                       |
| 颜色名称          | 冷日光                            |
| 色度坐标 X ( 标称 ) | 313                            |
| 色度坐标 Y ( 标称 ) | 337                            |
| 相关色温 ( 标称 )   | 6500 K                         |


|                 |                                      |
|-----------------|--------------------------------------|
| 光效 ( 额定 )( 标称 ) | 63 lm/W                              |
| 操作和电气           |                                      |
| 纹频率             | 50 or 60 Hz                          |
| 输入频率            | 50 或 60 Hz                           |
| 功耗              | 70 W                                 |
| 灯具电流 ( 标称 )     | 312 mA                               |
| 功率系数 ( 小数 )     | 0.6                                  |
| 电压 ( 标称 )       | 220–240 V                            |
| 产品数据            |                                      |
| 订单产品名称          | ESSENTIAL 70W CDL E27 220-240V 1CC/6 |
| 完整的产品名称         | ESSENTIAL 70W CDL E27 220-240V 1CC/6 |

ESSENTIAL

|                |                 |
|----------------|-----------------|
| 完整产品代码         | 692341076895400 |
| 订购代码           | 929689844999    |
| 材料编号 (12NC)    | 929689844999    |
| 计算器 - 每包数量     | 1               |
| EAN/UPC - 产品/箱 | 6923410768954   |

|                  |               |
|------------------|---------------|
| 计算器 - 每个外包装箱中的包数 | 6             |
| EAN/UPC - 案例     | 6923410769043 |

二维绘图



| Product                              | D (max) | C (max)  | F (max) |
|--------------------------------------|---------|----------|---------|
| ESSENTIAL 70W CDL E27 220-240V 1CC/6 | 67.9 mm | 332.5 mm | 87 mm   |

