



Energy Saver Reflectors

BC-EL/A R20 13W 3/1

Looking for an energy saver that doesn't look like one? The Philips EnergySaver family provides energy efficient lighting options that don't just provide similar light as your standard incandescent light bulb, they also have the same classic shapes. Philips Energy Saver reflector flood compact fluorescents reduce operating costs without sacrificing light quality compared to incandescent equivalents. With dimmable and hard glass options, they are ideal for recessed and track lighting indoors and outdoors.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Switching Cycle	4,000
Rated Lifetime (Hours)	8,000 hour(s)
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Color Code	827 [CCT of 2700K]
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	36 lm/W
Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	13 W


Lamp Current (Nom)	220 mA
Power Factor (Fraction)	0.55
Voltage (Nom)	110-127 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	EL/A R20
Approval and Application	
Mercury (Hg) Content (Nom)	1.5 mg
Product Data	
Order product name	BC-EL/A R20 13W 3/1
Order code	929689963502
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	3

Energy Saver Reflectors

Material Nr. (12NC)	929689963502
Full product name	BC-EL/A R20 13W 3/1
EAN/UPC - Case	50046677426830

EAN/UPC - Product/Case	046677426835
------------------------	--------------

Dimensional drawing



Product	D (max)	C (max)	F (max)
BC-EL/A R20 13W 3/1	64 mm	113 mm	43.5 mm

