



Energy Saver Decoratives

EL/A FAN 5W 6/1

Philips Energy Saver Decorative CFLs provide energy savings and reduce operating costs without sacrificing quality of light compared to incandescent equivalents.

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Product data


General Information			
Cap-Base	E26 [Single Contact Medium Screw]	Input Frequency	50 or 60 Hz
Switching Cycle	5,000	Power Consumption	5 W
Rated Lifetime (Hours)	8,000 hour(s)	Lamp Current (Nom)	80 mA
Lighting Technology	Compact Fluorescent Integrated	Power Factor (Fraction)	0.55
		Voltage (Nom)	110-127 V
Light Technical		Controls and Dimming	
Color Code	827 [CCT of 2700K]	Dimmable	No
Color Designation	Warm White (WW)		
Chromaticity Coordinate X (Nom)	463	Mechanical and Housing	
Chromaticity Coordinate Y (Nom)	420	Bulb Shape	EL/A FAN
Correlated Color Temperature (Nom)	2700 K		
Luminous Efficacy (rated) (Nom)	43 lm/W	Approval and Application	
		Mercury (Hg) Content (Max)	5 mg
Operating and Electrical			
Line Frequency	50 or 60 Hz		

Energy Saver Decoratives

Product Data	
Order product name	EL/A FAN 5W 6/1
Order code	929689984003
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929689984003

Full product name	EL/A FAN 5W 6/1
EAN/UPC - Case	50046677417470
EAN/UPC - Product/Case	046677417475

Dimensional drawing



Product	D (max)	C (max)	F (max)
EL/A FAN 5W 6/1	54 mm	104 mm	45.5 mm

