



# MASTER PL-Electronic

## MASTER PLE-C 11W/827 E27 230-240V 1CT/6

Non-covered energy-saving MASTER lamps for professional use

### Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

### Product data


General Information		LLMF At End Of Nominal Lifetime (Nom) 65 %	
Cap-Base	E27 [E27]		
Nominal lifetime	15,000 hour(s)		
Switching Cycle	20,000		
Rated Lifetime (Hours)	15,000 hour(s)		
Lighting Technology	Compact Fluorescent Integrated		
Light Technical		Operating and Electrical	
Color Code	827 [CCT of 2700K]	Line Frequency	50 or 60 Hz
Luminous Flux (Min)	540 lm	Input Frequency	50 or 60 Hz
Luminous Flux	600 lm	Power Consumption	11 W
Color Designation	Warm White (WW)	Lamp Current (Nom)	75 mA
Chromaticity Coordinate X (Nom)	466	Power Factor (Fraction)	0.62
Chromaticity Coordinate Y (Nom)	422	Voltage (Nom)	230-240 V
Correlated Color Temperature (Nom)	2700 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	55 lm/W	Dimmable	No
Color rendering index (CRI)	82	Mechanical and Housing	
		Bulb Shape	Stick

MASTER PL-Electronic

Approval and Application	
Mercury (Hg) Content (Nom)	1.41 mg
Energy Consumption kWh/1000 h	11 kWh
Product Data	
Order product name	MASTER PLE-C 11W/827 E27 230-240V 1CT/6
Full product name	MASTER PLE-C 11W/827 E27 230-240V 1CT/6
Full product code	871150026368100

Order code	26368100
Material Nr. (12NC)	929730982709
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500263681
Numerator - Packs per outer box	6
EAN/UPC - Case	8718291685470

Dimensional drawing



Product	D (max)	C (max)	F (max)
MASTER PLE-C 11W/827 E27 230-240V 1CT/6	28.0 mm	141.2 mm	40.3 mm

