



G3 LED Garage Luminaire

G3, Type 5, 2 LED arrays, 85W, 32 LEDs, 800mA, Neutral White, Generation 2

G3, Type 5, 2 LED arrays, 85W, 32 LEDs, 800mA, Neutral White, Generation 2 – 117 lm/W

The Gardco G3 parking garage luminaire combines excellent performance with value, providing one of the most energy efficient lighting solutions for the energy and budget conscious. A complete selection of optical systems are available, including a concentrated downlight for use at entrances or at higher mounting heights. G3 luminaires are available with dimming, as well as motion response technology to expand potential energy savings. The G3 is also available with the LimeLight Wireless Lighting Control System.

Product data

General Information	
Lamp Source Code	LED
Colour Temperature	4000K
CRI	70
Photometric Distribution Type	Type V
Mounting	Surface
B.U.G. Rating	B4U0G2
Operating and Electrical	
Voltages	120/208/240/277/347/480/UNIV V
Luminaire Input Watts	85

Mechanical and Housing	
Shape	Square
Material	Aluminum
Approval and Application	
Safety Listing	UL
Energy Certifications	DLC Standard
DesignLights Consortium Qualified Product List	DesignLights Consortium Qualified Product List
IP Rating	IP66

G3 LED Garage Luminaire

Initial Performance (IEC Compliant)	
Luminaire Lumens	10020
Efficacy	117 lm/W
Product Data	
Order product name	G3, Type 5, 2 LED arrays, 85W, 32 LEDs, 800mA, Neutral White, Generation 2

Order code	G3-5-32L-800-NW-G2
Material Nr. (12NC)	GAR1007245
Catalog Number	G3-5-32L-800-NW-G2
Catalog Number Description	G3, Type 5, 2 LED arrays, 85W, 32 LEDs, 800mA, Neutral White, Generation 2

