



# G3 LED Garage Luminaire

**G3, Type 5, 2 LED arrays, 64W, 32 LEDs, 600mA, Neutral White, Generation 2, w/ Diffuse Lens**

G3, Type 5, 2 LED arrays, 64W, 32 LEDs, 600mA, Neutral White, Generation 2, w/ Diffuse Lens - 103 lm/W

The Gardco G3 parking garage luminaire combines excellent performance with value, providing one of the most energy efficient lighting solutions for the energy and budget conscious. A complete selection of optical systems are available, including a concentrated downlight for use at entrances or at higher mounting heights. G3 luminaires are available with dimming, as well as motion response technology to expand potential energy savings. The G3 is also available with the LimeLight Wireless Lighting Control System.

## Product data

General Information		Mechanical and Housing	
Lamp Source Code	LED	Shape	Square
Colour Temperature	4000K	Material	Aluminum
CRI	70		
Photometric Distribution Type	Type V	Approval and Application	
Mounting	Surface	Safety Listing	UL
B.U.G. Rating	B2U0G1	IP Rating	IP66
Operating and Electrical		Initial Performance (IEC Compliant)	
Voltages	120/208/240/277/347/480/UNIV V	Luminaire Lumens	6532
Luminaire Input Watts	64	Efficacy	103 lm/W

# G3 LED Garage Luminaire

Product Data	
Order product name	G3, Type 5, 2 LED arrays, 64W, 32 LEDs, 600mA, Neutral White, Generation 2, w/ Diffuse Lens
Order code	G3-5DL-32L-600-NW-G2
Material Nr. (12NC)	GAR4004337

Catalog Number	G3-5DL-32L-600-NW-G2
Catalog Number Description	G3, Type 5, 2 LED arrays, 64W, 32 LEDs, 600mA, Neutral White, Generation 2, w/ Diffuse Lens

