



SoftView LED parking garage luminaire (SVPG)

SoftView LED parking garage, 168 LEDs, 1800mA, Neutral White, Concentrated Downlight

SoftView LED parking garage, 168 LEDs, 1800mA, Neutral White, Concentrated Downlight - 102 lm/W

Philips Gardco SoftView LED parking garage luminaires feature edge lit technology, providing visual comfort with minimal glare to enhance the user experience. An added uplight feature reduces the cave effect for an increased sense of security. SoftView features multiple optical distributions, lumen packages and mounting options providing you with the ideal solution for your garage lighting needs. Optional emergency battery backup available for path of egress lighting and is integral to the luminaire.

Product data

General Information		Efficacy 102 lm/W	
Lamp Source Code	LED		
Colour Temperature	4000K	Product Data	
Photometric Distribution Type	Downlight	Order product name	SoftView LED parking garage, 168 LEDs, 1800mA, Neutral White, Concentrated Downlight
Mounting	Surface Suspended	Catalog Number	SVPG-168L-1800-NW-CD
Operating and Electrical		Order code	GAR7003008
Luminaire Input Watts	85	Catalog Number Description	SoftView LED parking garage, 168 LEDs, 1800mA, Neutral White, Concentrated Downlight
Voltages	120/208/240/277/347/480/UNIV V	Material Nr. (12NC)	GAR7003008
Mechanical and Housing			
Shape	Round		
Initial Performance (IEC Compliant)			
Luminaire Lumens	8614		

SoftView LED parking garage luminaire (SVPG)

