



# SoftView LED parking garage luminaire (SVPG)

SoftView LED parking garage, 168 LEDs, 800mA, Neutral White, Type V

SoftView LED parking garage, 168 LEDs, 800mA, Neutral White, Type V - 110 lm/W

Philips Gardco SoftView LED parking garage luminaires feature edge lit technology, providing visual comfort with minimal glare to enhance the user experience. An added upright feature reduces the cave effect for an increased sense of security. SoftView features multiple optical distributions, lumen packages and mounting options providing you with the ideal solution for your garage lighting needs. Optional emergency battery backup available for path of egress lighting and is integral to the luminaire.

## Product data

General Information		Efficacy	
Lamp Source Code	LED	Efficacy	110 lm/W
Colour Temperature	4000K	Product Data	
Photometric Distribution Type	Type V	Order product name	SoftView LED parking garage, 168 LEDs, 800mA, Neutral White, Type V
Mounting	Surface Suspended	Catalog Number	SVPG-168L-800-NW-5
Operating and Electrical		Order code	GAR7003011
Luminaire Input Watts	35	Catalog Number Description	SoftView LED parking garage, 168 LEDs, 800mA, Neutral White, Type V
Voltages	120/208/240/277/347/480/UNIV V	Material Nr. (12NC)	GAR7003011
Mechanical and Housing			
Shape	Round		
Initial Performance (IEC Compliant)			
Luminaire Lumens	3951		

## SoftView LED parking garage luminaire (SVPG)

