



104 LED Sconce

104L LED Sconce, Type 2, 65W, 16 LED, Neutral white

104L LED Sconce, Type 2, 65W, 16 LED, Neutral white – 89 lm/W

Gardco 104 LED half cylinder high performance sconce luminaires are designed to integrate naturally to wall surfaces. 104 LED luminaires are available with three (3) different distribution patterns, providing full cutoff performance (in the normal downlight position) and featuring LED arrays. Luminaires provide performance excellence and advanced Gardco LED thermal management technology. High performance Class 1 LED systems offer potential energy savings of 50 % or more compared to HID systems. 104 LED luminaires are also available with Automatic Profile Dimming, increasing savings by an additional 33%.

Product data

General information	
Lamp Source Code	LED
Colour Temperature	4000 K
CRI	70
Photometric Distribution Type	Type II
Mounting	Wall
B.U.G. Rating	B2U0G1
Number Of Pieces	1
Buy American Compliant Products	Yes
Operating and electrical	
Voltages	120/208/240/277/347/480 V
Luminaire Input Watts	64
Conduit Connection	7/8 inch knockout

Mechanical and housing	
Shape	Round
Enclosure	Metal and Plastic
Approval and application	
Safety Listing	UL
Energy Certifications	cULus
Initial performance (IEC compliant)	
Luminaire Lumens	5743
Efficacy	89 lm/W
Application conditions	
Ambient temperature range	-40 to +40 °C
Max Ambient Temp	+40 °C

104 LED Sconce

Min Ambient Temp	-40 °C
Min Ambient Temp-DUP(do not use)	-40 °C
Product data	
Order product name	104L LED Sconce, Type 2, 65W, 16 LED, Neutral white

Order code	104L-16L-1200-NW-G1-2
Material Nr. (12NC)	GAR7003385
Catalog Number	104L-16L-1200-NW-G1-2
Catalog Number Description	104L LED Sconce, Type 2, 65W, 16 LED, Neutral white

