



# 161 LED Sconce

## 161, Gen 2, 92 LEDs, 600mA, Type 4, Neutral White

161, Gen 2, 92 LEDs, 600mA, Type 4, Neutral White – 112 lm/W

The Gardco LED Wall Sconce 161 is an enlarged and enhanced version of the 121, providing performance capability up to that of a 400W metal halide wall sconce, while using considerably less energy. Designed for mounting heights from 15 to 20 feet, the 161 offers exceptional performance, allowing a reduction in the total pole requirements on a site. The styling of the 161 also complements the PureForm site luminaires. The sloped surface ribs of its die cast aluminum housing create a distinctly unique aesthetic element, while performing important functions in the Gardco thermal management system.

### Product data

General information	
Lamp Source Code	LED
Colour Temperature	4000 K
CRI	70
Photometric Distribution Type	Type IV
Mounting	Wall
B.U.G. Rating	B3U0G3
Number Of Pieces	1
Buy American Compliant Products	Yes
Operating and electrical	
Voltages	120/208/240/277/347/480 V
Luminaire Input Watts	180
Conduit Connection	7/8 inch knockout
Mechanical and housing	
Material	Aluminum

Enclosure	Metal and Plastic
Approval and application	
Safety Listing	UL
Energy Certifications	DLC Standard cULus
Initial performance (IEC compliant)	
Luminaire Lumens	20300
Efficacy	112 lm/W
Application conditions	
Ambient temperature range	-40 to +40 °C
Max Ambient Temp	+40 °C
Min Ambient Temp	-40 °C
Min Ambient Temp-DUP(do not use)	-40 °C

161 LED Sconce

Product data	
Order product name	161, Gen 2, 92 LEDs, 600mA, Type 4, Neutral White
Order code	161L-92L-600-NW-G2-4
Material Nr. (12NC)	GAR7003691

Catalog Number	161L-92L-600-NW-G2-4
Catalog Number Description	161, Gen 2, 92 LEDs, 600mA, Type 4, Neutral White

