



# R6 Bollard

## Bollard, Aluminum, 100W MH, 120V, Type V, Refractor Bowl, Round

Bollard, Aluminum, 100W MH, 120V, Type V, Refractor Bowl, Round

The R6 aluminum bollard is a versatile bollard luminaire ideal for commercial applications. It is available in incandescent, CFL, MH and HPS with wattages up to 100W. Also available with LED sources in warm and neutral CCT. Reflectors include Type V refractor bowl and a Type V specular aluminum internal cone with a stabilized, clear acrylic lens. A thermoset polyester powdercoat finish is electrostatically and available in three finishes plus an optional CraftStone™ finish. The RD6 luminaire features a 6" diameter body that's easy to lamp.

### Product data

General Information	
Lamp Source Code	Metal Halide
Lamp Watts	100
Number of Lamps	1
Mounting	Ground / Floor

  

Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	100

Product Data	
Order product name	Bollard, Aluminum, 100W MH, 120V, Type V, Refractor Bowl, Round
Order code	RF6
Material Nr. (12NC)	HAD70000051
Catalog Number	RF6
Catalog Number Description	Bollard, Aluminum, 100W MH, 120V, Type V, Refractor Bowl, Round