



# FX1 Floodlight LED

## FX1, Generation 2, 32 LEDs, 4000K, 350 mA, Round Spot

FX1, Generation 2, 32 LEDs, 4000K, 350 mA, Round Spot – 93 lm/W

The FX1 and FX2 LED Floodlights have a sleek, rugged design with precision injection molded optics for superior lighting performance. Numerous optical distributions, mounting options and accessories including glare control provide versatility for use in many outdoor lighting applications.

### Product data

General Information	
Lamp Source Code	LED
Colour Temperature	4000K
CRI	70
Photometric Distribution Type	Horizontal Spot
Mounting	Ground / Floor Slip Fitter Wall
Operating and Electrical	
Voltages	120/208/240/277/347/480/UNIV V
Luminaire Input Watts	35
Mechanical and Housing	
Material	Aluminum
Approval and Application	
Safety Listing	UL
Energy Certifications	DLC Standard
DesignLights Consortium Qualified Product List	DesignLights Consortium Qualified Product List

IP Rating	IP66
Vibration Rating	3.0G
Initial Performance (IEC Compliant)	
Luminaire Lumens	4213
Efficacy	93 lm/W
Product Data	
Order product name	FX1, Generation 2, 32 LEDs, 4000K, 350 mA, Round Spot
Order code	FX132-G2-RSP-N-3
Material Nr. (12NC)	HAD70000067
Catalog Number	FX132-G2-RSP-N-3
Catalog Number Description	FX1, Generation 2, 32 LEDs, 4000K, 350 mA, Round Spot

## FX1 Floodlight LED

