



FX2 Floodlight LED

FX2, Generation 2, 160 LEDs, 4000K, 530 mA, Round Spot

FX2, Generation 2, 160 LEDs, 4000K, 530 mA, Round Spot – 94 lm/W

The FX1 and FX2 LED Floodlights have a sleek, rugged design with precision injection molded optics for superior lighting performance. Numerous optical distributions, mounting options and accessories including glare control provide versatility for use in many outdoor lighting applications.

Product data

General Information	
Lamp Source Code	LED
Colour Temperature	4000K
CRI	70
Photometric Distribution Type	Horizontal Spot
Mounting	Ground / Floor Slip Fitter
Operating and Electrical	
Voltages	120/208/240/277/347/480/UNIV V
Luminaire Input Watts	261
Mechanical and Housing	
Material	Aluminum
Approval and Application	
Safety Listing	UL
Energy Certifications	DLC Standard
DesignLights Consortium Qualified Product List	DesignLights Consortium Qualified Product List

IP Rating	IP66
Vibration Rating	1.5G
Initial Performance (IEC Compliant)	
Luminaire Lumens	29496
Efficacy	94 lm/W
Product Data	
Order product name	FX2, Generation 2, 160 LEDs, 4000K, 530 mA, Round Spot
Order code	FX2160-G2-RSP-N-5
Material Nr. (12NC)	HAD70000139
Catalog Number	FX2160-G2-RSP-N-5
Catalog Number Description	FX2, Generation 2, 160 LEDs, 4000K, 530 mA, Round Spot

FX2 Floodlight LED

