



FlexScape Accent BL9

Accent (BL9), BL9DW-AS7, BL9DW-HS7, Aluminum, 2W, 12V, Medium

Accent (BL9), BL9DW-AS7, BL9DW-HS7, Aluminum, 2W, 12V, Medium

Philips Hadco FlexScape LED accent luminaire BL9 brings landscape lighting to the next level. Designed for optimal LED performance, it provides the lighting professional with countless low-voltage options. The luminaire's rugged die-cast aluminum housing features low-energy outdoor lighting. Convenient beam adjustability makes for easy on-site lighting effect changes. The lockable aiming is well- suited for accenting objects, textures, walls, trees, etc. This all-weather luminaire comes with 100% molded silicone gaskets.

Product data

General Information	
Lamp Source Code	LED
Lamp Watts	2
Colour Temperature	3000K
CRI	70
Operating and Electrical	
Luminaire Input Watts	1
Voltages	12 V
Initial Performance (IEC Compliant)	
Luminaire Lumens	132

Product Data	
Order product name	Accent (BL9), BL9DW-AS7, BL9DW-HS7, Aluminum, 2W, 12V, Medium
Commercial Code	BL9
Order code	BL9
Catalog Number Description	Accent (BL9), BL9DW-AS7, BL9DW-HS7, Aluminum, 2W, 12V, Medium
Service / Spec Smart	-
Material Nr. (12NC)	HAD70000395