



# FlexScape Accent BL9

Accent (BL9), BL9DW-AS7, BL9DW-HS7,  
Aluminum, 2W, 12V, Large

Accent (BL9), BL9DW-AS7, BL9DW-HS7, Aluminum, 2W, 12V,  
Large

Hadco FlexScape LED accent luminaire BL9 brings landscape lighting to the next level. Designed for optimal LED performance, it provides the lighting professional with countless low-voltage options. The luminaire's rugged die-cast aluminum housing features low-energy outdoor lighting. Convenient beam adjustability makes for easy on-site lighting effect changes. The lockable aiming is well- suited for accenting objects, textures, walls, trees, etc. This all-weather luminaire comes with 100% molded silicone gaskets.

## Product data

| General Information                 |         |
|-------------------------------------|---------|
| Lamp Source Code                    | LED     |
| Lamp Watts                          | 2       |
| Number of Lamps                     | 1       |
| Colour Temperature                  | 3000K   |
| CRI                                 | 70      |
| Mounting                            | NPT/NPS |
| Operating and Electrical            |         |
| Voltages                            | 12 V    |
| Luminaire Input Watts               | 2       |
| Initial Performance (IEC Compliant) |         |
| Luminaire Lumens                    | 112     |

| Product Data               |  |
|----------------------------|--|
| Order product name         | Accent (BL9), BL9DW-AS7, BL9DW-HS7, Aluminum, 2W, 12V, Large |
| Order code                 | BL9  |
| Material Nr. (12NC)        | HAD70000397  |
| Catalog Number             | BL9  |
| Catalog Number Description | Accent (BL9), BL9DW-AS7, BL9DW-HS7, Aluminum, 2W, 12V, Large |