



# i25 Inground

## Inground, 70W MH T6, Spot w/ Multi-directional Spread Lens, 120V

Inground, 70W MH T6, Spot w/ Multi-directional Spread Lens, 120V

The revolutionary i2.5 composite inground provides optimum performance in a small aperture luminaire. Patented design elements including a hinged lens ring, potted factory seal, cool lens option and only 2 screws that do not require a torque wrench – the i2.5 reinforces HADCO's position as the leader in landscape lighting. Now available with LED

### Product data

General Information	
Lamp Source Code	Ceramic Metal Halide
Lamp Watts	70
Number of Lamps	1
Mounting	In Ground
Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	70

Product Data	
Order product name	Inground, 70W MH T6, Spot w/ Multi-directional Spread Lens, 120V
Order code	I25-SP70T6-IMSLR
Material Nr. (12NC)	HAD70000501
Catalog Number	I25-SP70T6-IMSLR
Catalog Number Description	Inground, 70W MH T6, Spot w/ Multi-directional Spread Lens, 120V