



MicroSquare gen2 suspended

MicroSquare gen2 Suspended Direct/Indirect LED, 5900 lm/4ft, 3000/3500/4000K Direct/Indirect, Flush Silk Lens Down - Asymmetric Wide-Throw Lens Up

MicroSquare gen2 Suspended Direct/Indirect LED, 5900 lm/4ft, 3000/3500/4000K Direct/Indirect, Flush Silk Lens Down - Asymmetric Wide-Throw Lens Up - 113 lm/W

Ledelite's MicroSquare gen2 has been re-engineered to furnish your space with the highest quality, discreet, narrow lines of continuous light. Elegant, low glare illumination with wide-throw upper and lower distributions improve visual comfort while allowing increased fixture spacing. This in turn, helps reduce initial and operating costs.

Product data

General Information		Luminaire Input Watts 49	
Lamp Source Code	LED		
Colour Temperature	3000/3500/4000K	Mechanical and Housing	
CRI	80	Shape	Linear
Photometric Distribution Type	Direct/Indirect	Initial Performance (IEC Compliant)	
Mounting	Suspended	Luminaire Lumens	5900
Operating and Electrical		Efficacy	113 lm/W
Voltages	120/277/347 V		

MicroSquare gen2 suspended

Product Data

Order product name	MicroSquare gen2 Suspended Direct/Indirect LED, 5900 lm/4ft, 3000/3500/4000K Direct/Indirect, Flush Silk Lens Down - Asymmetric Wide-Throw Lens Up
Order code	2206LxBLW
Material Nr. (12NC)	LED04286

Catalog Number	2206LxBLW
Catalog Number Description	MicroSquare gen2 Suspended Direct/Indirect LED, 5900 lm/4ft, 3000/3500/4000K Direct/Indirect, Flush Silk Lens Down - Asymmetric Wide-Throw Lens Up

