



TruGroove suspended

TruGroove Suspended Direct LED, 1500 lm/4ft, 3000/3500/4000K Direct, Asymmetric MesoOptics Lens

TruGroove Suspended Direct LED, 1500 lm/4ft, 3000/3500/4000K Direct, Asymmetric MesoOptics Lens - 89 lm/W

TruGroove LED is driving performance beyond the edge. Innovative optics deliver exceptional uniformity and wide row spacing from a 3" aperture continuous line-of light. An extended family and refined design are perfect for lighting any professional space.

Product data

General Information	
Lamp Source Code	LED
Colour Temperature	3000/3500/4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Suspended
Operating and Electrical	
Voltages	120/277/347 V
Luminaire Input Watts	15.2
Mechanical and Housing	
Shape	Linear

Initial Performance (IEC Compliant)	
Luminaire Lumens	1500
Efficacy	89 lm/W
Product Data	
Order product name	TruGroove Suspended Direct LED, 1500 lm/4ft, 3000/3500/4000K Direct, Asymmetric MesoOptics Lens
Order code	2901LxKWN
Material Nr. (12NC)	LED04369
Catalog Number	2901LxKWN
Catalog Number Description	TruGroove Suspended Direct LED, 1500 lm/4ft, 3000/3500/4000K Direct, Asymmetric MesoOptics Lens