



# TruGroove Recessed

## TruGroove Recessed Performance LED, 4000 lm/4ft, 3000/3500/4000K Direct, Regressed MesoOptics Lens

TruGroove Recessed Performance LED, 4000 lm/4ft,  
3000/3500/4000K Direct, Regressed MesoOptics Lens - 89 lm/W

TruGroove Recessed delivers unrivaled performance and a truly innovative design – making a definitive statement in any architectural space. TruGroove Recessed corners provide endless opportunities for creative freedom with geometric patterns in walls and ceilings.

### Product data

General Information	
Colour Temperature	3000/3500/4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Recessed franse vertaling
Operating and Electrical	
Luminaire Input Watts	41.8
Voltages	120/277/347 V
Mechanical and Housing	
Shape	Linear
Initial Performance (IEC Compliant)	
Luminaire Lumens	4000

Efficacy	89 lm/W
Product Data	
Order product name	TruGroove Recessed Performance LED, 4000 lm/4ft, 3000/3500/4000K Direct, Regressed MesoOptics Lens
Commercial Code	3901LxDR
Order code	3901LxDR
Catalog Number Description	TruGroove Recessed Performance LED, 4000 lm/4ft, 3000/3500/4000K Direct, Regressed MesoOptics Lens
Service / Spec Smart	-
Material Nr. (12NC)	LED04535