



Jump Suspended/ Surface

Jump Suspended Asymmetric LED, 3100 lm/4ft, 3000/3500/4000K Direct, Ribbed MesoOptics Lens - Splash/Pixel

Jump Suspended Asymmetric LED, 3100 lm/4ft,
3000/3500/4000K Direct, Ribbed MesoOptics Lens - Splash/
Pixel - 96 lm/W

Jump's contemporary aesthetic combines the latest lighting technologies with texture, pattern, and rhythm along an uninterrupted end to end continuum of luminance.

Product data

General Information		Initial Performance (IEC Compliant)	
Lamp Source Code	LED	Luminaire Lumens	3100
Colour Temperature	3000/3500/4000K	Efficacy	96 lm/W
CRI	80		
Photometric Distribution Type	Asymmetric	Product Data	
Mounting	Suspended	Order product name	Jump Suspended Asymmetric LED, 3100 lm/4ft, 3000/3500/4000K Direct, Ribbed MesoOptics Lens - Splash/Pixel
Operating and Electrical		Order code	1208LxEQx
Voltages	120/277/347 V	Material Nr. (12NC)	LED04597
Luminaire Input Watts	32.6	Catalog Number	1208LxEQx
Mechanical and Housing		Catalog Number Description	Jump Suspended Asymmetric LED, 3100 lm/4ft, 3000/3500/4000K Direct, Ribbed MesoOptics Lens - Splash/Pixel
Shape	Linear		

Jump Suspended/Surface

