



# SlimSurface LED Downlight

**SlimSurface LED downlight, 7-inch round, surface mount, 80 CRI, 3000K CCT, 1000 lm, 120V, Standard (TRIAC) dimming, wet location, Matte White Finish**

SlimSurface LED downlight, 7-inch round, surface mount, 80 CRI, 3000K CCT, 1000 lm, 120V, Standard (TRIAC) dimming, wet location, Matte White Finish - 71 lm/W

SlimSurface LED is a low profile downlight intended for ceiling or wall mount applications. This 0.625" thick luminaire offers the appearance of a recessed downlight but is actually surface mounted.

## Product data

General Information	
Lamp Source Code	LED
Colour Temperature	3000K
CRI	80
Downlight Type	Open Downlight
Photometric Distribution Type	Direct
Mounting	Surface Wall
Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	14

Mechanical and Housing	
Aperture Size Code	7 in
Shape	Round
Initial Performance (IEC Compliant)	
Luminaire Lumens	1000
Efficacy	71 lm/W
Product Data	
Order product name	SlimSurface LED downlight, 7-inch round, surface mount, 80 CRI, 3000K CCT, 1000 lm, 120V, Standard (TRIAC) dimming, wet location, Matte White Finish

# SlimSurface LED Downlight

Order code	S7R830K10
Material Nr. (12NC)	LIGU60011118
Catalog Number	S7R830K10
Catalog Number Description	SlimSurface LED downlight, 7-inch round, surface mount, 80 CRI, 3000K CCT, 1000 lm,120V, Standard (TRIAC) dimming, wet location, Matte White Finish

