



OmniSpot LED Track Heads

OmniSpot 600lm PremiumWhite 90 CRI (Narrow Spot, Spot, Narrow Flood, Flood)

OmniSpot 600lm PremiumWhite 90 CRI (Narrow Spot, Spot, Narrow Flood, Flood) – 115 lm/W

Our upgraded OmniSpot LED cylinder is now available with Signify's AccuRender technology – a highly efficacious CRI 90. Designed to meet the most demanding retail challenges through sleek and discrete aesthetics, while providing a high center beam candlepower and lighting performance. OmniSpot allows for less than 1" of space between the track head and track in the ceiling, making it a perfect fit for a variety of applications.

Product data

| | | | |
|---------------------------------|----------------------------------|--|-------------|
| General information | | Luminaire Input Watts 6 | |
| Lamp Source Code | LED | Mechanical and housing | |
| Colour Temperature | 3000 K | Shape | Round |
| CRI | 90 | Approval and application | |
| Downlight Type | Accent Adjustable | Energy Certifications | Energy Star |
| Mounting | Track | Initial performance (IEC compliant) | |
| Adapter | Lightolier Halo Juno Global Tek | Luminaire Lumens | 600 lm |
| Fixture Finish | White;Black;Aluminium;Custom RAL | Efficacy | 115 lm/W |
| Number Of Pieces | 1 | | |
| Grade | Specification Grade | | |
| Operating and electrical | | | |
| Voltages | 120 V | | |

OmniSpot LED Track Heads

| Product data | |
|---------------------|--|
| Order product name | OmniSpot LED 600lm 90CRI 27K Black ELV |
| Order code | LCL06PW30XXTE/LLMXX |
| Material Nr. (12NC) | LIGU60014628 |
| Catalog Number | LCL06PW30XXTE/LLMXX |

| Catalog Number | Description |
|----------------|---|
| | OmniSpot 600lm PremiumWhite 90 CRI (Narrow Spot, Spot, Narrow Flood, Flood) |

