



OmniSpot LED Track Heads

OmniSpot LED 600lm 90CRI 30K White ELV CrispWhite

OmniSpot LED 600lm 90CRI 30K White ELV CrispWhite

OmniSpot LED cylinder is designed to meet the most demanding retail challenges through sleek and discrete aesthetics while providing a high center beam candlepower and efficacy performance. OmniSpot LED cylinder allows for less than 1" of space between the track head and track in the ceiling.

Product data

General Information	
Lamp Source Code	LED
Colour Temperature	3000
CRI	90
Mounting	Track
Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	6
Mechanical and Housing	
Shape	Round

Initial Performance (IEC Compliant)	
Luminaire Lumens	600
Product Data	
Order product name	OmniSpot LED 600lm 90CRI 30K White ELV CrispWhite
Order code	LC06930WTECW
Material Nr. (12NC)	LIGU60014630
Catalog Number	LC06930WTECW
Catalog Number Description	OmniSpot LED 600lm 90CRI 30K White ELV CrispWhite