



OmniSpot LED Track Heads

OmniSpot 2000lm CrispWhite 90 CRI (Narrow Spot, Spot, Narrow Flood, Flood)

OmniSpot 2000lm CrispWhite 90 CRI (Narrow Spot, Spot, Narrow Flood, Flood) – 102 lm/W

Our upgraded OmniSpot LED cylinder is now available with Signify's AccuRender technology – a highly efficacious CRI 90. Designed to meet the most demanding retail challenges through sleek and discrete aesthetics, while providing a high center beam candlepower and lighting performance. OmniSpot allows for less than 1" of space between the track head and track in the ceiling, making it a perfect fit for a variety of applications.

Product data

General information		Luminaire Input Watts 24 W	
Lamp Source Code	LED	Mechanical and housing	
Colour Temperature	3000 K	Shape	Round
CRI	90	Approval and application	
Downlight Type	Accent Adjustable	Energy Certifications	Energy Star
Mounting	Track	Initial performance (IEC compliant)	
Adapter	Lightolier Halo Juno Global Tek	Luminaire Lumens	2000 lm
Fixture Finish	White;Black;Aluminium;Custom RAL	Efficacy	102 lm/W
Number Of Pieces	1		
Grade	Specification Grade		
Operating and electrical			
Voltages	120 V		

OmniSpot LED Track Heads

Product data

Order product name	OmniSpot LED 2000lm 80CRI 40K White ELV
Order code	LCL20CW30XXTE/LLMXX
Material Nr. (12NC)	LIGU60014641
Catalog Number	LCL20CW30XXTE/LLMXX

Catalog Number	Description	OmniSpot 2000lm CrispWhite 90 CRI (Narrow Spot, Spot, Narrow Flood, Flood)
----------------	-------------	--

